

# **PM-33 Detector**

**Highly Sensitive Gamma Detector** 

**Radiation Detection Division** 

**Health Physics** 

The PM-33 is a scintillation probe for detection of gamma radiation from 0 to 50,000 cps with a sensitivity of 4,500 CPS per uSv/h (<sup>137</sup>Cs)

The PM-33 contains a highly efficient, hermetically sealed, NaI(TI) scintillator, 3" diameter and 3" thick, coupled to a 3" photomultiplier tube. This is encased in a rugged, splash proof housing for protection against shock, vibration and humidity. The probe also contains a high voltage power supply, single channel analyzer (SCA), pulse shaper, GM saturation indicator, detector identifier and malfunction detection circuitry. This configuration minimizes noise, improving sensitivity and stability.

The PM-33 can be used as an detector to the RAM DA-2000. When used in conjunction with the TeleMeterextremely sensitive Environmental Monitor when connected directly to the TeleMeter or as an external

#### Stand Alone Measuring Range: Background to 10 uSv/h

**Environmental Monitor Measuring Range:** Background to 15 mSv/h (1.5 R/h) where the internal GM tube in the TeleMeter is activated to measure from 10 uSv/h to 15 mSv/h

### Features



## **PM-33 Detector**

<b>Radiation Detected:</b>	Gamma above 50 keV
Sensitivity ( <sup>137</sup> Cs):	4,500 CPS per uSv/h
Scintillator:	Nal(TI) 3" diameter, 3" high
Energy Calibration:	Optional factory calibrated single channel analyzer (SCA) within the energy range
Count Rate Range:	0 - 50,000 cps
Output Signals:	TTL pulses.
	Detector status: ID, OK, malfunction, overflow
Temperature Range:	Operation: -10°C to +50°C (15°F - 122°F)
	Storage: -20°C to +60°C (-5°F - 140°F)
Humidity Range:	40% to 95% RH (non condensing)
Dimensions:	365mm (14.4") length, 105 mm (4.13") width
Weight:	2.95kg (6.5 lbs)
Casing:	Aluminum, splash proof

# **Ordering Information**

**BAK-1515 PM-33 Detector** 

ROTEM INDUSTRIES reserves the right to change specifications without advance notice





**ROTEM INDUSTRIES LTD. Radiation Detection Division** Mishor Yamin, D.N. Arava 8680600, Israel Tel. +972-8-6564780/1, Fax. +972-8-6573252 E-mail. sales@rotemi.co.il Web: www.rotem-radiation.co.il

11/04/2018